

# 単焦点サポートレンズシリーズ

## サポート160

### 特長特長

●遠用エリアとサポートエリアの2つのエリアで眼をサポートするサポートレンズシリーズ。

・近くを見る際の調節力を補助し、眼が楽に感じられる

・慣れやすくすっきりとした自然な掛け心地で、どのような場面でもご利用頂ける常用レンズ

・近くをみる環境が多く、視緊張による眼の疲れや肩・首のこりなどを感じている10代~30代の方におすすめ

●プリズムシニング加工。



●UV吸収剤練り込み素材

●紫外線UV-A・Bカット

球面	乱視 (-)												
	度数	-	0	0	1	1	1	2	2	2	3	3	3
0.00		0	0	1	1	1	2	2	2	3	3	3	4
0.25		2	2	3	3	3	4	4	4	5	5	5	6
0.50		5	5	6	6	6	7	7	7	8	8	8	9
0.75													
1.00													
1.25													
1.50													
1.75													
2.00													
2.25													
2.50													
2.75													
3.00													
3.25													
3.50													
3.75													
4.00													
4.25													
4.50													
4.75													
5.00													
5.25													
5.50													
5.75													
6.00													
6.25													
6.50													
6.75													
7.00													
7.25													
7.50													
7.75													
8.00													
8.25													
8.50													
8.75													
9.00													
9.25													
9.50													
9.75													
10.00													

球面	乱視 (+)												
	度数	+	0	0	1	1	1	2	2	2	3	3	3
0.00		0	0	1	1	1	2	2	2	3	3	3	4
0.25		2	2	3	3	3	4	4	4	5	5	5	6
0.50		5	5	6	6	6	7	7	7	8	8	8	9
0.75													
1.00													
1.25													
1.50													
1.75													
2.00													
2.25													
2.50													
2.75													
3.00													
3.25													
3.50													
3.75													
4.00													

混合乱視 (MIX)										度数	
0	0	1	1	1	2	2	2	3	3		4
0	0	1	1	1	2	2	2	3	3	4	±
5	7	0	2	5	7	0	2	5	7	0	0.25
0	5	0	5	0	5	0	5	0	5	0	0.50
											0.75
											1.00
											1.25
											1.50
											1.75
											2.00
											2.25
											2.50
											2.75
											3.00
											3.25
											3.50
											3.75



### 仕様

- 材質 高屈折プラスチックレンズ
- 屈折率 1.60
- 比重 1.31
- アッペ数 42

### 特注条件

プリズム	○	0.25△~3.00△まで(0.25とび) スリ残しが出ることがあります。
偏心	×	—
外径指定	○	プラス・ミックスのみ 径小は55mmまで(1mmキザミ)
フチ厚指定	○	—
スレンダー/薄型加工	○	プラス・ミックスのみ
カラー	○	アリアーテ・見本色 受注可 DLCカラー受注可
UVカット	○	標準装備
注意事項		●遠用度数測定位置で、レンズメーカーの十字が出ませんが、中心の点をフィッティングポイントとして加工をお願い致します。 ●レンズに上下方向がありますので、ご注意ください。 (「R」が書いてある方が上方向です。)